



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ACP3033BC 30A 3W3P P&S Plug (600VAC/250VDC)

*Appleton/Oz Gedney*

Catalog Number	ACP3033BC
Manufacturer	Appleton/Oz Gedney
Description	Powerlite Grounding Style 1 Metallic Clamping Ring Plug, Number Of Poles: 3, Number Of Wires: 3, Wire Size: 10 - 6 Awg (Building), 10 - 8 Awg (Extra Flex), Amperage Rating: 30 Amp, Voltage Rating: 600 Vac At 50 - 400 HZ, 250 VDC, Phase:
Weight per unit	5.1 (lbs/each)
Product Category	Pin & Sleeve Devices

### Features

amperage rating	30
connection	Pressure Wire Terminal
Material	Copperfree (4/10 Of 1 PCT Maximum) Aluminum
Number of Wires	3
Phase	3
Poles	3
Voltage Rating	600 VAC At 50 - 400 HZ, 250 VDC
Wire Size	10 - 6

### Descriptions

Description	30A 3W3P P&S PLUG (600VAC/250VDC)
extra long description	APP ACP3033BC 30AMP PLUG 3W-3P STYL
Long Description	Powerlite Grounding Style 1 Metallic Clamping Ring Plug, Number Of Poles: 3, Number Of Wires: 3, Wire Size: 10 - 6 AWG (Building), 10 - 8 AWG (Extra Flex), Amperage Rating: 30 AMP, Voltage Rating: 600 VAC At 50 - 400 HZ, 250 VDC, Phase:
Product Type	30AMP Plug 3W-3P Style 1
Special Features	Designed to supply power to portable or fixed electrical equipment such as motor generator units, welders, pumps, compressors, cellular relay stations and similar apparatus;Grounding style: Shell only;Ideal for use on shipping docks, ports and other ship to shore applications;Locking screw and slot prevents plug cable collar from backing off;Natural finish glass filled polyester insulating blocks;Plug and receptacle combination is NEMA 4X rated when clamping ring is fully tightened on receptacle;Rough usag



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Appleton
GTIN	00781381440417
Manufacturers Part Number	ACP3033BC
UPC	781381440417

## Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Grounding Style 1 Metallic Clamping Ring Plug

## Packaging

Carton	6
Weight Per each	5.05

## Uses, Certifications, and Standards

Application	For ADR3033 Receptacle And ARC3033BC Connector Body
environmental conditions	Temperature Rating: -40 To 107 DEG C
nema rating	3, 3R, 4, 4X
standard	CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917