



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street
88201-0000, NM Roswell
Phone: 575-208-1571
Fax: 575-208-1572



ACP6044BC 60A 4W4P P&S Plug (600VAC/250VDC)

Appleton/Oz Gedney

Catalog Number	ACP6044BC
Manufacturer	Appleton/Oz Gedney
Description	Powerlite Grounding Style 1 Metallic Clamping Ring Plug, Number Of Poles: 4, Number Of Wires: 4, Wire Size: 6 - 2 Awg (Building), 6 - 4 Awg (Extra Flex), Amperage Rating: 60 Amp, Voltage Rating: 600 Vac At 50 - 400 HZ, 250 VDC, Phase: 3
Weight per unit	3.0 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	60
connection	Pressure Wire Terminal
Material	Copperfree (4/10 Of 1 PCT Maximum) Aluminum
Number of Wires	4
Phase	3
Poles	4
Voltage Rating	600 VAC At 50 - 400 HZ, 250 VDC
Wire Size	6 - 2

Descriptions

Description	60A 4W4P P&S PLUG (600VAC/250VDC)
extra long description	APP ACP6044BC 60A CLAMP RING PLUG 4
Long Description	Powerlite Grounding Style 1 Metallic Clamping Ring Plug, Number Of Poles: 4, Number Of Wires: 4, Wire Size: 6 - 2 AWG (Building), 6 - 4 AWG (Extra Flex), Amperage Rating: 60 AMP, Voltage Rating: 600 VAC At 50 - 400 HZ, 250 VDC, Phase: 3
Product Type	60A Clamp Ring Plug 4W4P ST1
Special Features	Designed to supply power to portable or fixed electrical equipment such as motor generator units, welders, pumps, compressors, cellular relay stations and similar apparatus;Grounding style: Shell only;Ideal for use on shipping docks, ports and other ship to shore applications;Locking screw and slot prevents plug cable collar from backing off;Natural finish glass filled polyester insulating blocks;Plug and receptacle combination is NEMA 4X rated when clamping ring is fully tightened on receptacle;Rough usag



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street
88201-0000, NM Roswell
Phone: 575-208-1571
Fax: 575-208-1572

Manufacturer Information

Brand	Appleton
GTIN	00781381440233
Manufacturers Part Number	ACP6044BC
UPC	781381440233

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Grounding Style 1 Metallic Clamping Ring Plug

Packaging

Carton	6
Weight Per each	3.02

Uses, Certifications, and Standards

Application	For ADR6044 Receptacle And ARC6044BC Connector Body
environmental conditions	Temperature Rating: -40 To 107 DEG C
nema rating	3, 3R, 4, 4X
standard	CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917