

# Specifications



Photo is representative



## Eaton AGC-1/10-R

Eaton AGC series Fast-acting fuse 0.10A, 250 Vac, 32 Vdc (self certified), AGC-1-10-R

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series AGC fast-acting glass tube fuse
<b>CATALOG NUMBER</b>	AGC-1/10-R
<b>UPC</b>	051712654883
<b>PRODUCT LENGTH/DEPTH</b>	1.25 in
<b>PRODUCT HEIGHT</b>	0.25 in
<b>PRODUCT WIDTH</b>	0.25 in
<b>PRODUCT WEIGHT</b>	0.006 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant



Powering Business Worldwide

## Product specifications

<b>USED WITH</b>	out axial leads
<b>AMPERAGE RATING</b>	0.10 A
<b>INTERRUPT RATING</b>	35 AIC at 250 Vac 10 kAIC at 125 Vac
<b>FUSE INDICATOR</b>	Non-indicating
<b>CONNECTION</b>	Ferrule end x ferrule end
<b>RESPONSE TIME</b>	60 min at 135%, 120 sec at 200%
<b>MATERIAL</b>	Glass tube Nickel-plated brass end cap construction
<b>QUANTITY</b>	5
<b>VOLTAGE RATING</b>	250 Vac, 32 Vdc (self certified)
<b>TYPE</b>	Electronic
<b>APPLICATION</b>	Electronic circuits

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton AGC fast-acting glass tube fuses data-sheet</a> <a href="#">Eaton Specification Sheet - AGC-1/10-R</a>
--------------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton AGC-1/10-R

Eaton AGC series Fast-acting fuse 0.10A, 250 Vac, 32 Vdc (self certified), AGC-1-10-R

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series AGC fast-acting glass tube fuse
<b>CATALOG NUMBER</b>	AGC-1/10-R
<b>UPC</b>	051712654883
<b>PRODUCT LENGTH/DEPTH</b>	1.25 in
<b>PRODUCT HEIGHT</b>	0.25 in
<b>PRODUCT WIDTH</b>	0.25 in
<b>PRODUCT WEIGHT</b>	0.006 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant



Powering Business Worldwide

## Product specifications

<b>USED WITH</b>	out axial leads
<b>AMPERAGE RATING</b>	0.10 A
<b>INTERRUPT RATING</b>	35 AIC at 250 Vac 10 kAIC at 125 Vac
<b>FUSE INDICATOR</b>	Non-indicating
<b>CONNECTION</b>	Ferrule end x ferrule end
<b>RESPONSE TIME</b>	60 min at 135%, 120 sec at 200%
<b>MATERIAL</b>	Glass tube Nickel-plated brass end cap construction
<b>QUANTITY</b>	5
<b>VOLTAGE RATING</b>	250 Vac, 32 Vdc (self certified)
<b>TYPE</b>	Electronic
<b>APPLICATION</b>	Electronic circuits

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton AGC fast-acting glass tube fuses data-sheet](#)

[Eaton Specification Sheet - AGC-1/10-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

