



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGC1610R 1-6/10A 250V 1/4X1-1/4 Rohs Fa Glass Fuse *Bussmann Fuses*

|                  |  |
|------------------|--|
| Catalog Number   | AGC1610R   |
| Manufacturer     | Bussmann Fuses   |
| Description      | Eaton Agc Series Fast-Acting Fuse 1.6A, 250 Vac, 32 VDC (Self Certified), Agc-1-6-10-R |
| Weight per unit  | 0.0060 (lbs/each)  |
| Product Category | Small Dimension Fuses  |

### Features

|                  |  |
|------------------|--|
| amperage rating  | 1.6A   |
| connection       | Ferrule End X Ferrule End                          |
| dimensions       | 1.2500 IN X 0.2500 IN X 0.2500 IN                  |
| interrupt rating | 100 AIC at 250 Vac10 kAIC at 125 Vac               |
| Material         | Glass tubeNickel-plated brass end cap construction |
| Response Time    | 60 min at 135%, 120 sec at 200%                    |
| Voltage Rating   | 250 Vac, 32 Vdc (self certified)                   |

### Dimensions and Weight

|      |                                   |
|------|-----------------------------------|
| Size | 1/4 In Diameter X 1-1/4 In Length |
|------|-----------------------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 1-6/10A 250V 1/4X1-1/4 ROHS FA GLASS FUSE  |
| extra long description | BUSS AGC-1-6/10-R BUSS SMALL DIMENS  |
| Features               | Fast-acting, glass tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's AGC fast-acting, glass tube 1/4" x 1-1/4" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase w |
| Long Description       | Eaton AGC series Fast-acting fuse 1.6A, 250 Vac, 32 Vdc (self certified), AGC-1-6-10-R   |
| Product Type           | Buss Small Dimension Fuse  |
| Special Features       | Interrupt Rating 100 Amp at 250 Vac, 10000 Amp at 250 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Compliant   |

### Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | Eaton Bussmann series |
| GTIN                      | 00051712654869        |
| Manufacturers Part Number | AGC-1-6/10-R          |
| UPC                       | 051712654869          |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | GLASS FUSES (and ceramic)   |
| Type                 | Fast-acting glass tube fuse |

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 5     |
| Weight Per each | 0.006 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Ind Facilities & Factories - Facility: Safety and Security Systems |
| standard    | CE Marked,RoHS Compliant   |