



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604



AGC2 2A 250V 1/4X1-1/4 Rohs Fa Glass Fuse *Bussmann Fuses*

Catalog Number	AGC2
Manufacturer	Bussmann Fuses
Description	Buss Agc-2 Agc Glass Fuse - 1/4 X 1
Weight per unit	0.0060 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	2 AMP
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	250 VAC

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	2A 250V 1/4X1-1/4 ROHS FA GLASS FUSE
Long Description	BUSS AGC-2 AGC GLASS FUSE - 1/4 x 1
Product Type	Agc Glass Fuse - 1/4 X 1-1/4 - 2 Amp
Special Features	Interrupt Rating 100 Amp at 250 Vac, 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712703840
Manufacturers Part Number	AGC-2
UPC	051712703840

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	5
Weight Per each	0.006



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604

Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA