

Specifications



Eaton AGC-30-R

Eaton ABC series Fast-acting fuse, 9A, 250 Vac, 125 Vdc, 32 Vac (self certified)

General specifications

PRODUCT NAME	Eaton Bussmann series AGC fast-acting glass tube fuse
CATALOG NUMBER	AGC-30-R
UPC	051712655187
PRODUCT LENGTH/DEPTH	1.25 in
PRODUCT HEIGHT	0.25 in
PRODUCT WIDTH	0.25 in
PRODUCT WEIGHT	0.004 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant



Powering Business Worldwide

Product specifications

USED WITH	out axial leads
AMPERAGE RATING	30 A
INTERRUPT RATING	1 kAIC at 32 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 120 sec at 200%
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	32 Vac, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS	Eaton AGC fast-acting glass tube fuses data-sheet
	Eaton Specification Sheet - AGC-30-R

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

