



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

310 Interstate Blvd
29615-0000, SC Greenville
Phone: 864-735-7911
Fax: 000-000-0000



AGX20 20A 32V 1/4X1 Fa Glass Fuse

Bussmann Fuses

Catalog Number	AGX20
Manufacturer	Bussmann Fuses
Description	Eaton Agx Series Fast-Acting Fuse 20A, 250 Vac, 32 VDC
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	20
connection	Ferrule End X Ferrule End
dimensions	1.0000 IN X 0.2500 IN X 0.2500 IN
interrupt rating	200 AIC at 125 Vac1 kAIC at 32 Vac
Material	Glass Fuse;Nickel-plated brass end cap construction
Response Time	4 hr at 110%, 60 min at 135%, 2 min at 200%
Voltage Rating	250 Vac, 32 Vdc

Dimensions and Weight

Size	0.25 In Diameter X 1.00 In Length
------	-----------------------------------

Descriptions

Description	20A 32V 1/4X1 FA GLASS FUSE
extra long description	BUSS AGX-20 AGX GLASS FUSE - 1/4" x
Features	Fast-acting, glass tube 1/4" x 1" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block or fuse clip. Eaton's AGX fast-acting, glass tube 1/4" x 1" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip.
Long Description	Eaton AGX Series Fast-acting fuse 20A, 250 Vac, 32 Vdc
Product Type	Agx Glass Fuse - 1/4" X 1" - 20 Amp
Special Features	Glass tube

Manufacturer Information

Brand	Eaton
GTIN	00051712704830
Manufacturers Part Number	AGX-20
UPC	051712704830

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

310 Interstate Blvd
29615-0000, SC Greenville
Phone: 864-735-7911
Fax: 000-000-0000

Packaging

Carton	5
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	Not Applicable