Specifications

Eaton AH1224V

Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 20A, Industrial, Wall, 120/277V, Back and side, Screw, Ivory, Four-way, Brass, Terminals: 0.031 in, Polycarbonate

General specifications	
PRODUCT NAME	Eaton Arrow Hart industrial grade toggle switch
CATALOG NUMBER	AH1224V
UPC	032664734939
PRODUCT LENGTH/DEPTH	1.03 in
PRODUCT HEIGHT	2.4 in
PRODUCT WIDTH	1.3 in
PRODUCT WEIGHT	0.01 lb
COMPLIANCES	NAFTA
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Industrial grade toggle switch

Powering Business Worldwide

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	20A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Industrial
WIRING METHOD	Back and side
SWITCH TYPE	Four-way
MOUNTING METHOD	Wall
CONNECTOR TYPE	Screw
MATERIAL	Polycarbonate
NUMBER OF WAYS	Four-way
ALLOWABLE WIRE SIZE	#14-10 AWG
TORQUE RATING	14 lbf-inch
TERMINAL ENCLOSURE MATERIAL	Brass
TERMINALS	0.031 in
COLOR	Ivory

Resources

MULTIMEDIA	Arrow Hart - Connecting Safety to Reliability since 1890
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AH1224V Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Specifications

Eaton AH1224V

Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 20A, Industrial, Wall, 120/277V, Back and side, Screw, Ivory, Four-way, Brass, Terminals: 0.031 in, Polycarbonate

General specifications	
PRODUCT NAME	Eaton Arrow Hart industrial grade toggle switch
CATALOG NUMBER	AH1224V
UPC	032664734939
PRODUCT LENGTH/DEPTH	1.03 in
PRODUCT HEIGHT	2.4 in
PRODUCT WIDTH	1.3 in
PRODUCT WEIGHT	0.01 lb
COMPLIANCES	NAFTA
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Industrial grade toggle switch

Powering Business Worldwide

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	20A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Industrial
WIRING METHOD	Back and side
SWITCH TYPE	Four-way
MOUNTING METHOD	Wall
CONNECTOR TYPE	Screw
MATERIAL	Polycarbonate
NUMBER OF WAYS	Four-way
ALLOWABLE WIRE SIZE	#14-10 AWG
TORQUE RATING	14 lbf-inch
TERMINAL ENCLOSURE MATERIAL	Brass
TERMINALS	0.031 in
COLOR	Ivory

Resources

MULTIMEDIA	Arrow Hart - Connecting Safety to Reliability since 1890
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AH1224V Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.