

Specifications

Eaton AH430C12W

Eaton Arrow Hart pin and sleeve connector, IP69K Rated, #10 -#2 AWG, 30A, Extra Heavy-Duty, 125/250V, Back wire, Orange, Nickel plated brass, IP67, IP69K, Nylon, Three-pole, Four-wire, grounding, 0.433-0.985in (1.10-2.5cm), Female, Nylon



General specifications

PRODUCT NAME	Eaton Arrow Hart pin and sleeve connector
CATALOG NUMBER	AH430C12W
UPC	032664732706
PRODUCT LENGTH/DEPTH	10.375 in
PRODUCT HEIGHT	4.813 in
PRODUCT WIDTH	4.75 in
PRODUCT WEIGHT	1.207 lb
CERTIFICATIONS	cRUus
PRODUCT TYPE	Pin and Sleeve connector

Product specifications

TYPE	Connector
AMPERAGE RATING	30A
VOLTAGE RATING	125/250 V
CONTACT MATERIAL	Nickel plated brass
APPLICATION	Industrial, food and beverage, wastewater treatment
NUMBER OF WIRES	4 Grounding
NUMBER OF POLES	Three-pole
CORD DIAMETER	0.433-0.985in (1.10-2.5cm)
ENVIRONMENTAL RESISTANCE	IP67 IP69K
COLOR	Orange
GENDER	Female
ALLOWABLE WIRE SIZE	#10-2 AWG
TORQUE RATING	10 lbf-inch
DESIGN TYPE	Pin and sleeve connector
FACE/BODY MATERIAL	Nylon
MATERIAL	Nylon

Resources

BROCHURES	Eaton IEC 60309 Arrow Hart pin and sleeve devices brochure
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AH430C12W 20A and 30A IEC 309 Watertight pin and sleeve devices spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

