

Specifications

Eaton AH430P5W

Eaton Arrow Hart pin and sleeve plug, IP69K Rated, #10 -#2 AWG, 30A, 3Ø 600V, Back wire, Black, Nickel plated brass, IP67, Nylon, Three-pole, Four-wire, grounding, 0.433-0.985in (1.10-2.5cm), Male, 15 HP, Nylon, Three-phase

General specifications

PRODUCT NAME	Eaton Arrow Hart pin and sleeve plug
CATALOG NUMBER	AH430P5W
UPC	040893619675
PRODUCT LENGTH/DEPTH	10.375 in
PRODUCT HEIGHT	4.813 in
PRODUCT WIDTH	4.75 in
PRODUCT WEIGHT	0.997 lb
CERTIFICATIONS	cRUus
PRODUCT TYPE	Pin and Sleeve plug



Powering Business Worldwide

Product specifications

TYPE	Plug
AMPERAGE RATING	30A
VOLTAGE RATING	600 V
CONTACT MATERIAL	Nickel plated brass
APPLICATION	Industrial, food and beverage, wastewater treatment
NUMBER OF WIRES	Grounding 4
NUMBER OF POLES	Three-pole
CORD DIAMETER	0.433-0.985in (1.10-2.5cm)
PHASE	Three-phase
ENVIRONMENTAL RESISTANCE	IP69K IP67
COLOR	Black
GENDER	Male
HORSEPOWER	15 hp
ALLOWABLE WIRE SIZE	#10-2 AWG
TORQUE RATING	10 lbf-inch
DESIGN TYPE	Pin and sleeve plug
FACE/BODY MATERIAL	Nylon
MATERIAL	Nylon

Resources

BROCHURES	Eaton IEC 60309 Arrow Hart pin and sleeve devices brochure
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AH430P5W 20A and 30A IEC 309 Watertight pin and sleeve devices spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton AH430P5W

Eaton Arrow Hart pin and sleeve plug, IP69K Rated, #10 -#2 AWG, 30A, 3Ø 600V, Back wire, Black, Nickel plated brass, IP67, Nylon, Three-pole, Four-wire, grounding, 0.433-0.985in (1.10-2.5cm), Male, 15 HP, Nylon, Three-phase

General specifications

PRODUCT NAME	Eaton Arrow Hart pin and sleeve plug
CATALOG NUMBER	AH430P5W
UPC	040893619675
PRODUCT LENGTH/DEPTH	10.375 in
PRODUCT HEIGHT	4.813 in
PRODUCT WIDTH	4.75 in
PRODUCT WEIGHT	0.997 lb
CERTIFICATIONS	cRUus
PRODUCT TYPE	Pin and Sleeve plug



Powering Business Worldwide

Product specifications

TYPE	Plug
AMPERAGE RATING	30A
VOLTAGE RATING	600 V
CONTACT MATERIAL	Nickel plated brass
APPLICATION	Industrial, food and beverage, wastewater treatment
NUMBER OF WIRES	Grounding 4
NUMBER OF POLES	Three-pole
CORD DIAMETER	0.433-0.985in (1.10-2.5cm)
PHASE	Three-phase
ENVIRONMENTAL RESISTANCE	IP69K IP67
COLOR	Black
GENDER	Male
HORSEPOWER	15 hp
ALLOWABLE WIRE SIZE	#10-2 AWG
TORQUE RATING	10 lbf-inch
DESIGN TYPE	Pin and sleeve plug
FACE/BODY MATERIAL	Nylon
MATERIAL	Nylon

Resources

BROCHURES	Eaton IEC 60309 Arrow Hart pin and sleeve devices brochure
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AH430P5W 20A and 30A IEC 309 Watertight pin and sleeve devices spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

