

Specifications



Eaton AH5269

Eaton Arrow Hart ultra grip straight blade connector, #16 - #12 AWG, 15A, Industrial, 125V, Back wire, Black, Brass, Nylon, 5-15R, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Nylon, Core pack

General specifications

PRODUCT NAME	Eaton Arrow Hart ultra grip straight blade connector
CATALOG NUMBER	AH5269
UPC	032664737534
PRODUCT LENGTH/DEPTH	2.23 in
PRODUCT HEIGHT	2.1 in
PRODUCT WIDTH	3.61 in
PRODUCT WEIGHT	0.195 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed NOM Federal Specification Classification W-C-596F
PRODUCT TYPE	Ultra grip



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	15A
NEMA CONFIGURATION	5-15R
TORQUE RATING	14 lbf-inch
VOLTAGE RATING	125V
WIRING METHOD	Back wire

Product Specifications

ALLOWABLE WIRE SIZE	#16-12 AWG
APPLICATION	Industrial
CONNECTION TYPE	Screw
CORD RANGE	0.33-0.66" in diameter
DESIGN TYPE	Straight blade
DEVICE GRADE	Extra heavy-duty industrial specification grade
DEVICE TYPE	Connector
NUMBER OF POLES	Two-pole
NUMBER OF WIRES	3
RECEPTACLE TYPE	Two-pole, three-wire, grounding
STYLE TYPE	Straight body
TYPE	Connector

Material Specifications

COLOR	Black
CONTACT MATERIAL	Brass
FACE/BODY MATERIAL	Nylon
MATERIAL	Nylon
PACKAGING TYPE	Core pack

Resources

MULTIMEDIA	Arrow Hart - Connecting Safety to Reliability since 1890
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AH5269 Industrial Grade Straight Blade Devices Spec Sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

