

Eaton AH8462AN

Catalog Number: AH8462AN

Eaton Arrow Hart extra heavy-duty angled plug , #12-4 AWG, 60A, Industrial range and dryer, 250V, Back wire, Gray, Brass, Nylon and Thermoplastic, 15-60P, Three-pole, four-wire, grounding, Screw, Nylon, Core pack

General specifications



Product Name

Eaton Arrow Hart extra heavy-duty angled plug

Catalog Number

AH8462AN

UPC

040893121734

Product Length/Depth

2.8 in

Product Height

2.92 in

Product Width

1.03 in

Product Weight

1.05 lb

Warranty

Refer to warranty document.

Certifications

UL

Federal Specification Classification 6233 01

Product specifications

Device type

Plug

Color

Gray

Face/body material

Thermoplastic

Nylon

Wiring method

Back wire

Material

Nylon

Allowable wire size

#12-4 AWG

Amperage Rating

60A

Number Of Poles

Three-pole

Contact material

Brass

Type

Angled plug

Device grade

Extra heavy-duty industrial specification grade

NEMA configuration

15-60P

Style type

Power, Angled body

Design type

Straight blade

Connection type

Screw

Number of wires

4

Receptacle type

Three-pole, four-wire, grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section A](#)

Specifications and datasheets

[Eaton Specification Sheet - AH8462AN](#)

Voltage rating

250V

Application

Industrial, range and dryer

Torque rating

30-35 lbf-inch

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)