

Eaton AHCL1430P

Catalog Number: AHCL1430P

Eaton Arrow Hart Color Coded Locking Plug, #14-8 AWG, 30A, Industrial, 125/250V, Back, Orange, Black, Ultra grip, Nylon, L14-30, Three-pole, Four-wire, Nylon, 0.38 - 1.16" (9.5 - 29.5mm), -40°C (w/o impact) to 60°C (-40°F to 140°F)



General specifications

Product Name	Catalog Number
Eaton Arrow Hart Color Coded Locking Plug	AHCL1430P
	UPC
	032664755675
Product Length/Depth	Product Height
2.13 in	2.92 in
Product Width	Product Weight
2.3 in	0.4 lb
Warranty	Compliances
Refer to warranty document.	RoHS Compliant
	NAFTA
Certifications	
cULus Listed	
NOM	

Product specifications

Special features

Voltage Color Coding

Color

Black

Orange

Face/body material

Nylon

Wiring method

Back

Material

Nylon

Allowable wire size

#14-8 AWG

Amperage Rating

30A

Number Of Poles

Three-pole

Type

Locking Plug

NEMA configuration

L14-30

Design type

Ultra grip

Number of wires

4

Operating temperature

-40 to 60 °C (-40 to 140 °F)

Voltage rating

125/250 V

Cord diameter

0.38-1.16 in (9.5-29.5 mm)

Application

Industrial

Torque rating

14-16 lbf-inch

Resources

Multimedia

[Arrow Hart industrial color coded locking devices](#)

[Eaton Arrow Hart color coded locking devices](#)

Specifications and datasheets

[Eaton Specification Sheet - AHCL1430P](#)

[Arrow Hart color coded industrial grade L14-30 locking devices spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)