

Eaton AHCL820P

Catalog Number: AHCL820P

Eaton Arrow Hart Color Coded Locking Plug, Locking Plug, #14-8 AWG, 20A, Industrial, 480V, Back, Red, Black, Ultra grip, Nylon, L8-20, Two-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm), -40°C (w/o impact) to 60°C (-40°F to 140°F)

General specifications

Product Name	Catalog Number
Eaton Arrow Hart Color Coded Locking Plug	AHCL820P
	UPC
	032664755774
Product Length/Depth	Product Height
2.23 in	2.69 in
Product Width	Product Weight
2.1 in	0.4 lb
Warranty	Compliances
Refer to warranty document.	RoHS Compliant
	NAFTA
Certifications	
cULus Listed	
NOM	



Product specifications

Special features

Voltage Color Coding

Color

Black

Red

Face/body material

Nylon

Wiring method

Back

Material

Nylon

Allowable wire size

#14-8 AWG

Amperage Rating

20A

Number Of Poles

Two-pole

Type

Locking Plug

NEMA configuration

L8-20

Design type

Ultra grip

Number of wires

3

Operating temperature

-40 to 60 °C (-40 to 140 °F)

Voltage rating

480 V

Cord diameter

0.38-1 in (9.5-25.4 mm)

Application

Industrial

Torque rating

For #10-14 AWG: 14-16 lbf-inch. For #8 AWG: 20 lbf-inch

Resources

Brochures

[Arrow Hart color coded locking devices sell sheet](#)

Multimedia

[Arrow Hart industrial color coded locking devices](#)

[Eaton Arrow Hart color coded locking devices](#)

Specifications and datasheets

[Eaton Specification Sheet - AHCL820P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)