

# Specifications

## Eaton AHDS30

Eaton motor control disconnect switch, #14-10 AWG, 30A, Industrial, Mounting feet/DIN rail, flush or 1/4" spacing, 600V, Gray, NEMA 4X, Enclosure: VALOX thermoplastic, Washdown, Three-pole, Three-phase, Rotary switch, Thermoplasti

### General specifications

|                             |                                       |
|-----------------------------|---------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton motor control disconnect switch |
| <b>CATALOG NUMBER</b>       | AHDS30                                |
| <b>UPC</b>                  | 032664741326                          |
| <b>PRODUCT LENGTH/DEPTH</b> | 8.75 in                               |
| <b>PRODUCT HEIGHT</b>       | 5 in                                  |
| <b>PRODUCT WIDTH</b>        | 5.68 in                               |
| <b>PRODUCT WEIGHT</b>       | 3.183 lb                              |
| <b>COMPLIANCES</b>          | RoHS Compliant                        |
| <b>CERTIFICATIONS</b>       | cULus Listed                          |
| <b>PRODUCT TYPE</b>         | Motor control disconnect switch       |

## Product specifications

|                          |                                                |
|--------------------------|------------------------------------------------|
| NEMA RATING              | 4X                                             |
| ENCLOSURE                | NEMA 4X                                        |
| TYPE                     | Motor control disconnect switch                |
| AMPERAGE RATING          | 30A                                            |
| VOLTAGE RATING           | 600 V                                          |
| NUMBER OF POLES          | Three-pole                                     |
| PHASE                    | Three-phase                                    |
| ENCLOSURE MATERIAL       | VALOX thermoplastic                            |
| APPLICATION              | Industrial                                     |
| DEVICE GRADE             | Industrial                                     |
| ENVIRONMENTAL CONDITIONS | Complex Washdown                               |
| SWITCH TYPE              | Rotary switch                                  |
| MOUNTING METHOD          | Flush or 1/4 in spacing Mounting feet/DIN rail |
| ALLOWABLE WIRE SIZE      | #14-10 AWG                                     |
| MATERIAL                 | Thermoplastic                                  |
| COLOR                    | Gray                                           |

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AHDS30](#)

[Non-fused 30 or 60 amp motor control disconnect switch spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

