

# Specifications

## Eaton AHDS60VFD

Eaton motor control disconnect switch, #14-4 AWG, 60A, Industrial, Mounting feet/DIN rail, flush or 1/4" spacing, 600V, Aux. contacts for VF drive (early-break), Gray, NEMA 4X, Enclosure: VALOX thermoplastic, Washdown, Three-phase, Rotary

### General specifications

<b>PRODUCT NAME</b>	Eaton motor control disconnect switch
<b>CATALOG NUMBER</b>	AHDS60VFD
<b>UPC</b>	032664741371
<b>PRODUCT LENGTH/DEPTH</b>	11 in
<b>PRODUCT HEIGHT</b>	5.5 in
<b>PRODUCT WIDTH</b>	7.5 in
<b>PRODUCT WEIGHT</b>	5.01 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	cULus Listed
<b>PRODUCT TYPE</b>	Motor control disconnect switch



Powering Business Worldwide

## Product specifications

<b>NEMA RATING</b>	4X
<b>ENCLOSURE</b>	NEMA 4X
<b>TYPE</b>	Motor control disconnect switch
<b>AMPERAGE RATING</b>	60A
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF POLES</b>	Three-pole
<b>PHASE</b>	Three-phase
<b>ENCLOSURE MATERIAL</b>	VALOX thermoplastic
<b>APPLICATION</b>	Industrial
<b>DEVICE GRADE</b>	Industrial
<b>CONTACT TYPE</b>	Auxiliary
<b>ENVIRONMENTAL CONDITIONS</b>	Complex Washdown
<b>SWITCH TYPE</b>	Rotary switch
<b>MOUNTING METHOD</b>	Mounting feet/DIN rail Flush or 1/4 in spacing
<b>ALLOWABLE WIRE SIZE</b>	#14-4 AWG
<b>MATERIAL</b>	Thermoplastic
<b>COLOR</b>	Gray

## Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AHDS60VFD](#)

[X-Switch motor controllers disconnect switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton AHDS60VFD

Eaton motor control disconnect switch, #14-4 AWG, 60A, Industrial, Mounting feet/DIN rail, flush or 1/4" spacing, 600V, Aux. contacts for VF drive (early-break), Gray, NEMA 4X, Enclosure: VALOX thermoplastic, Washdown, Three-phase, Rotary

### General specifications

<b>PRODUCT NAME</b>	Eaton motor control disconnect switch
<b>CATALOG NUMBER</b>	AHDS60VFD
<b>UPC</b>	032664741371
<b>PRODUCT LENGTH/DEPTH</b>	11 in
<b>PRODUCT HEIGHT</b>	5.5 in
<b>PRODUCT WIDTH</b>	7.5 in
<b>PRODUCT WEIGHT</b>	5.01 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	cULus Listed
<b>PRODUCT TYPE</b>	Motor control disconnect switch



Powering Business Worldwide

## Product specifications

<b>NEMA RATING</b>	4X
<b>ENCLOSURE</b>	NEMA 4X
<b>TYPE</b>	Motor control disconnect switch
<b>AMPERAGE RATING</b>	60A
<b>VOLTAGE RATING</b>	600 V
<b>NUMBER OF POLES</b>	Three-pole
<b>PHASE</b>	Three-phase
<b>ENCLOSURE MATERIAL</b>	VALOX thermoplastic
<b>APPLICATION</b>	Industrial
<b>DEVICE GRADE</b>	Industrial
<b>CONTACT TYPE</b>	Auxiliary
<b>ENVIRONMENTAL CONDITIONS</b>	Complex Washdown
<b>SWITCH TYPE</b>	Rotary switch
<b>MOUNTING METHOD</b>	Mounting feet/DIN rail Flush or 1/4 in spacing
<b>ALLOWABLE WIRE SIZE</b>	#14-4 AWG
<b>MATERIAL</b>	Thermoplastic
<b>COLOR</b>	Gray

## Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AHDS60VFD](#)

[X-Switch motor controllers disconnect switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

