

Eaton AHIG5262RN

Catalog Number: AHIG5262RN

Eaton Arrow Hart extra heavy-duty industrial specification grade duplex receptacle, #14 to 10 AWG, 15A, Flush, 125V, Back and side, Orange, Brass, High-impact nylon face, Glass-filled nylon base, 5-15R, Two-pole, three-wire, grounding, Screw, Core pack



General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty industrial specification grade duplex receptacle	AHIG5262RN
	UPC
	032664349904
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.89 in	0.37 lb
Warranty	Compliances
Refer to warranty document.	RoHS Compliant

Certifications

UL

NOM

Federal Specification Classification 6233

01

Product specifications

Device type

Receptacle

Color

Orange

Face/body material

High-impact nylon face

Glass-filled nylon base

Wiring method

Back and side

Features

Isolated ground

Terminal guards

Material

Glass-filled nylon

Mounting method

Flush

Allowable wire size

#14-10 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Duplex receptacle

Device grade

Extra heavy-duty industrial specification grade

NEMA configuration

5-15R

Style type

Standard

Design type

Straight blade

Connection type

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Arrow Hart extra heavy duty industrial grade isolated ground straight blade receptacles](#)

[Eaton Specification Sheet - AHIG5262RN](#)

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia