



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AN110 110 CFM 3.0 Sones Vent Fan

Broan/Nutone LLC

Catalog Number	AN110
Manufacturer	Broan/Nutone LLC
Description	Ventilation Fan, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UL, Hvi Approval; 120 Volt Ac At 60 Hertz Voltage Rating; 0.4 Amp Current Rating; 26 Gauge Rugged Galvanized Steel Housing Material; 110 CFM Air Flow Rate
Weight per unit	8.9 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	110 CFM
Current Rating	0.4 Amp
Duct Shape	Round IN
Duct Size	4 Inch Diameter
Grill Finish	White
Grill Shape	Rectangular
Grill Size	11-1/4 Inch Length x 12 Inch Width
Housing Shape	Rectangular
Sound Level	3 SONES
Ventilation Area	105 Square Foot (Bath Room)
Voltage Rating	120 Volt AC at 60 Hertz

Material, Color, and Finish

Grill Material	Polymeric
Housing Material	26 Gauge Rugged Galvanized Steel

Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height
------	---

Descriptions

Additional Information	Power Rating 47.3 Watt; Duct Mounting Direction Horizontal
Commodity Description	Exhaust Fans
Description	110 CFM 3.0 SONES VENT FAN
Long Description	VENTILATION FAN, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AC AT 60 HERTZ VOLTAGE RATING; 0.4 AMP CURRENT RATING; 26 GAUGE RUGGED GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE
Product Type	Ventilation Fan



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Broan/Nutone LLC
GTIN	00026715236541
Manufacturers Part Number	AN110
UPC	026715236541

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	CEILING

Packaging

Carton	1
Weight Per each	8.8999

Uses, Certifications, and Standards

Approval	UL, HVI
----------	---------