

Eaton AN16KN0A

Catalog Number: AN16KN0A

Eaton Freedom NEMA Starter, Full voltage non-reversing, C306 bi-metal overload relay, NEMA Size 3 open enclosure - 90 A, Horizontal mounting, 120/60 or 110/50 coil voltage



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN16KN0A
	UPC
	782113603896

Product Length/Depth	Product Height
5.94 in	11.35 in

Product Width	Product Weight
4.08 in	11 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

Catalog Notes

Heater Packs must be purchased separately

[NEMA frame size](#)

NEMA Size 3

[Relay](#)

C306 bi-metal

[Type](#)

Starter

[Special features](#)

Starter w/C306 bi-metal OLR

[Configuration](#)

Non-reversing

[Phase](#)

Three-phase

[Amperage Rating](#)

90 A

[Size](#)

3

[Horsepower](#)

25 hp at 208 V, 30 hp at 240 V, 50 hp at 480/600 V

[Mounting](#)

Horizontal

[Overload relay](#)

C306 bi-metal

[Coil voltage](#)

120/60 or 110/50

[Catalogs](#)

Eaton's Volume 5—Motor Control and Protection

[Drawings](#)

AN16KN0 2D Drawing Xchange

AN16KN0 3D Inventor

AN16KN0 3D Model Xchange

AN16KN0 AutoCAD 2D Footprint

AN16KN0 AutoCAD 2D Footprint (mm)

AN16KN0 2D PDF

[Specifications and datasheets](#)

Eaton Specification Sheet - AN16KN0A

Quick Selector - NEMA Contactors