

Eaton AN16SN0AB

Catalog Number: AN16SN0AB

Eaton Freedom NEMA motor control starter, NEMA Freedom Series Non-Reversing Reset Overload Relay Starter, 75 hp at 208V, 100 hp at 240V, 200 hp at 480,600V maximum horsepower, 120V/60 Hz or 110V/50 Hz coil voltage, 270A, Three-pole, Size 5



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN16SN0AB
	UPC
	782113971889

Product Length/Depth	Product Height
7.75 in	7.22 in

Product Width	Product Weight
12 in	25 lb

Warranty	Certifications
-----------------	-----------------------

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

CSA Certified

[Catalog Notes](#)

Heater Packs must be purchased separately

defaultTaxonomyAttributeLabel

Special features

Starter w/C306 bi-metal OLR

Phase

Three-phase

Number of Poles

Three-pole

Amperage Rating

270A

Size

5

Horsepower

75 hp at 208 V, 100 hp at 240 V, 200 hp at 480/600 V

Mounting

Horizontal

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[AN16SN0_B AutoCAD 2D Footprint](#)

[AN16SN0_B 2D Drawing Xchange](#)

[AN16SN0_B AutoCAD 2D Footprint \(mm\)](#)

[AN16SN0_B 3D Inventor](#)

[AN16SN0_B 3D Model Xchange](#)

[AN16SN0_B 2D PDF](#)

Specifications and datasheets

[Quick Selector - NEMA Contactors](#)

[Eaton Specification Sheet - AN16SN0AB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)