

Eaton AN19DN0C5E020

Catalog Number: AN19DN0C5E020

Eaton Freedom NEMA Starter, Full voltage non-reversing, C440 electronic overload relay, NEMA Size 1 open enclosure - 27 A, Horizontal mounting, 480/60 or 440/50 coil voltage, C440 standard feature set - 4–20 A



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN19DN0C5E020
	UPC
	786685417332
Product Length/Depth	Product Height
4.98 in	7.1 in
Product Width	Product Weight
2.6 in	4 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL	
CSA	
CE	
NEMA	

defaultTaxonomyAttributeLabel

Accessories

Freedom NEMA

NEMA frame size

NEMA Size 1

Relay

C440 electronic

Type

Starter

Special features

With C440 EOLR standard feature set, SEL reset, SEL class (10a, 10, 20, 30)

Configuration

Non-reversing

Amperage Rating

27 A

Size

1

Mounting

Horizontal

Overload relay

C440 electronic

Coil voltage

480/60 or 440/50

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

AN19DN0_5 AutoCAD 2D Footprint (mm)

AN19DN0_5 AutoCAD 2D Footprint

AN19DN0_5 3D Inventor

AN19DN0_5 2D Drawing Xchange

AN19DN0_5 2D PDF

AN19DN0_5 3D Model Xchange

Specifications and datasheets

Eaton Specification Sheet - AN19DN0C5E020



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia