

# Eaton AN19KN0A5E100

Catalog Number: AN19KN0A5E100

Eaton Freedom NEMA Starter, Full voltage non-reversing, C440 electronic overload relay, NEMA Size 3 open enclosure - 90 A, Horizontal mounting, 120/60 or 110/50 coil voltage, C440 standard feature set - 20–100 A



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Freedom NEMA motor control starter	AN19KN0A5E100
	<b>UPC</b>
	786685415529
<b>Product Length/Depth</b>	<b>Product Height</b>
5.92 in	11.4 in
<b>Product Width</b>	<b>Product Weight</b>
4.09 in	11 lb
<b>Warranty</b>	<b>Compliances</b>
1 year	RoHS Compliant
<b>Certifications</b>	
UL	
CSA	
CE	
NEMA	

## defaultTaxonomyAttributeLabel

### NEMA frame size

NEMA Size 3

### Relay

C440 electronic

### Type

Starter

### Special features

With C440 EOLR standard feature set, SEL reset, SEL class (10a, 10, 20, 30)

### Configuration

Non-reversing

### Amperage Rating

90 A

### Size

3

### Mounting

Horizontal

### Overload relay

C440 electronic

### Coil voltage

120/60 or 110/50

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - AN19KN0A5E100](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)