

Eaton AN19KN0A5G100

Catalog Number: AN19KN0A5G100

Eaton Freedom NEMA Starter, Full voltage non-reversing, C440 electronic overload relay, NEMA Size 3 open enclosure - 90 A, Horizontal mounting, 120/60 or 110/50 coil voltage, C440 ground fault feature set - 20–100 A



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN19KN0A5G100
	UPC
	786685415536
Product Length/Depth	Product Height
5.92 in	7 in
Product Width	Product Weight
4.09 in	10.4 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL	
CSA	
CE	
NEMA	

defaultTaxonomyAttributeLabel

Accessories

Freedom NEMA

NEMA frame size

NEMA Size 3

Relay

C440 electronic

Type

Starter

Special features

With C440 EOLR ground fault feature set, SEL reset, SEL class (10, 20)

Configuration

Non-reversing

Amperage Rating

90 A

Size

3

Mounting

Horizontal

Overload relay

C440 electronic

Coil voltage

120/60 or 110/50

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - AN19KN0A5G100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia