

Eaton AN19NN0A5E140

Catalog Number: AN19NN0A5E140

Eaton Freedom NEMA Starter, Full voltage non-reversing, C440 electronic overload relay, NEMA Size 4 open enclosure - 135 A, Horizontal mounting, 120/60 or 110/50 coil voltage, C440 standard feature set - 28–140 A



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN19NN0A5E140
	UPC
	786685575117

Product Length/Depth	Product Height
22 in	9 in

Product Width	Product Weight
13 in	27 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

NEMA frame size

NEMA Size 4

Relay

C440 electronic

Type

Starter

Configuration

Non-reversing

Amperage Rating

135 A

Size

NEMA size 4

Overload relay

C440 electronic

Coil voltage

120/60 or 110/50

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - AN19NN0A5E140](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)