

Eaton AN19SN0A5E300

Catalog Number: AN19SN0A5E300

Eaton Freedom NEMA Starter, Full voltage non-reversing, C440 electronic overload relay, NEMA Size 5 open enclosure - 270 A, Horizontal mounting, 120/60 or 110/50 coil voltage, C440 standard feature set - 60–300 A



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN19SN0A5E300
	UPC
	786685415765
Product Length/Depth	Product Height
8.08 in	17.81 in
Product Width	Product Weight
7 in	34.3 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL	
CSA	
CE	
NEMA	

defaultTaxonomyAttributeLabel

NEMA frame size

NEMA Size 5

Relay

C440 electronic

Type

Starter

Special features

With C440 EOLR standard feature set, SEL reset, SEL class (10a, 10, 20, 30)

Configuration

Non-reversing

Amperage Rating

270 A

Size

5

Mounting

Horizontal

Overload relay

C440 electronic

Coil voltage

120/60 or 110/50

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - AN19SN0A5E300](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)