

Eaton AN56DN0AB

Catalog Number: AN56DN0AB

Eaton Freedom NEMA motor control starter, Reversing Reset Overload Relay Starter, 2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V maximum horsepower, 120V/60 Hz or 110V/50 Hz coil voltage, 27A, Three-pole, Size 1



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN56DN0AB
	UPC
	782113972503

Product Length/Depth	Product Height
4.61 in	3.31 in

Product Width	Product Weight
4.38 in	2.6 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

Catalog Notes

Heater Packs must be purchased separately

defaultTaxonomyAttributeLabel

HP rating - max

2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V

Phase

Single-phase, three-phase

Amperage Rating

27A

Size

1

Resources

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Quick Selector - NEMA Contactors](#)

[Eaton Specification Sheet - AN56DN0AB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)