

Eaton AP20467

Catalog Number: AP20467

Eaton Crouse-Hinds series Arktite AP plug, 200A, 1.375-1.875", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Crimp/solder, 600 Vac/250 Vdc, 0.56" max

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite AP plug	AP20467
	UPC
	782274039909
Product Length/Depth	Product Height
14.75 in	6.75 in
Product Width	Product Weight
6.75 in	12.25 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

Product specifications

Amperage Rating

200A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cable diameter

1.375-1.875"

Termination style

Crimp/solder

Wire well size

0.56" max

Material

Copper-free aluminum

Resources

Catalogs

[Arktite 200A Metallic Plugs, Receptacles and Connectors catalog page](#)

Installation instructions

[IF 852 - Arktite AP Series, Model 80 200A/400A](#)

[IF 852A - Arktite AP Series, Model 80 200A with Mechanical Lugs](#)

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - AP20467](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)