# Eaton APR10467

## Catalog Number: APR10467

Eaton Crouse-Hinds series Arktite APR connector, 100A, 0.875-1.70", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

## General specifications



Product Name Catalog Number

Eaton Crouse-Hinds series Arktite APR APR10467

connector

**UPC** 

782274057002

Product Length/Depth Product Height

10.88 in 3.44 in

Product Width Product Weight

3.44 in 5.65 lb



## Certifications and compliances

#### Area classification

Ordinary/Non-Hazardous Locations

## Standards type

NEC/CEC

## **NEMA Rating**

4

## **Product specifications**

## Amperage Rating

100A

## Voltage rating

600 Vac/250 Vdc

## Frequency rating

50 to 400 Hz

## Grounding type

Style 2

## Configuration

Three-wire, four-pole

## Cable diameter

0.875-1.70"

#### Material

Copper-free aluminum

## Resources

## 3D CAD drawing package

Eaton Crouse-Hinds APR10467 3D drawing

#### Catalogs

Arktite 100A Metallic Plugs, Receptacles and Connectors catalog page

## Certification reports

Arktite Metallic Plugs, Receptacles and Connectors UL certification (APR)

#### Installation instructions

IF 1295 - Arktite APR 30, 60 and 100A Wiring Information

## Specifications and datasheets

Eaton Specification Sheet - APR10467



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia