DESCRIPTION

The APWR LED remote series is a UL924 code compliant solution for emergency lighting. It operates on 3.6 volts and can be powered from the APXH exit or APCH combo series. It is wet location listed and can be used indoors or outdoors. The two head versions will create 17 feet of emergency egress coverage. Housings color options are white or black.

| Catalog # | Туре |
|-------------|------|
| | |
| Project | |
| Comments | Date |
| | |
| Prepared by | |

SPECIFICATION FEATURES

Electrical

- 3.6V DC Input Voltage

Lampholder/Mounting Plate Construction

- Flame resistant and impact resistant, injection molded thermoplastic
- Lamp heads adjust 80° from vertical with 358° rotation
- vertical with 358° rotation Universal mounting plate
- Available in white or black

Code Compliance

- UL 924 Listed
- Wet Location Listed (APWR)
- 0 °C to 40 °C (32 °F to 104 °F) temperature rating
- California Energy Code compliant


Head/Lamp Data


- Long Life LED Emergency Heads
- Fully adjustable
- High impact thermoplastic
- Matches housing finish
- 3.6V, .78W DC Long Lasting LED Heads


Warranty

- Five-year warranty











Sure-Lites



APWR SERIES

REMOTE HEADS
LED EMERGENCY HEADS
WET LOCATION LISTED









ENERGY DATA

Power Consumption is equal to LED head wattage.

ORDERING INFORMATION

SAMPLE NUMBER: APWR2BK

| Series | Remote Heads | Housing Color | Catalog numbers |
|--------|---------------------------------------|--------------------------------|--------------------------------|
| APWR | 1 = one LED head 2 = two LED heads | _ = White BK = Black | APWR1, APWR2, APWR1BK, APWR2BK |

APWR SPACING

