



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ARC6034BC 60A 3W4P Conn Body Assembly

Appleton/Oz Gedney

Catalog Number	ARC6034BC
Manufacturer	Appleton/Oz Gedney
Description	Powertite Grounding Style 2 Connector Body, Number Of Poles: 4, Number Of Wires: 3, Wire Size: 6 - 2 Awg (Building), 6 - 4 Awg (Extra Flex), Amperage Rating: 60 Amp, Voltage Rating: 600 Vac At 50 - 400 HZ, 250 VDC, Phase: 3 PH, Material
Weight per unit	2.3 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	60
connection	Pressure Wire Terminal
Material	Copperfree (4/10 Of 1 PCT Maximum) Aluminum
Number of Wires	3
Phase	3
Poles	4
Voltage Rating	600 VAC At 50 - 400 HZ, 250 VDC
Wire Size	6 - 2 AWG (Building), 6 - 4 AWG (Extra Flex)

Descriptions

Description	60A 3W4P CONN BODY ASSEMBLY
extra long description	APP ARC6034BC 60A CONN BODY ASSY 4P
Long Description	Powertite Grounding Style 2 Connector Body, Number Of Poles: 4, Number Of Wires: 3, Wire Size: 6 - 2 AWG (Building), 6 - 4 AWG (Extra Flex), Amperage Rating: 60 AMP, Voltage Rating: 600 VAC At 50 - 400 HZ, 250 VDC, Phase: 3 PH, Material
Product Type	60A Conn Body Assy 4P S2
Special Features	Designed to supply power to portable or fixed electrical equipment such as motor generator units, welders, pumps, compressors, cellular relay stations and similar apparatus;Grounding style: Shell and extra pole;Ideal for use on shipping docks, ports and other ship to shore applications;Natural finish glass filled polyester insulating blocks;Rough usage construction;Suitable for use in locations where a weatherproof enclosure is required;Wire recess diameter: 5/16 IN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Appleton
GTIN	00781381440639
Manufacturers Part Number	ARC6034BC
UPC	781381440639

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Grounding Style 2 Connector Body

Packaging

Carton	1
Package	6
Weight Per each	2.25

Uses, Certifications, and Standards

Application	For ACP6034BC Metallic Clamping Ring Plug
nema rating	NEMA 3, 3R, 4, 4X
standard	CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917