

# Eaton ASZH240C300

Catalog Number: ASZH240C300

Eaton Cooper Power series secondary arrester, Storm Trapper HE, MCOV: 240 Vac, Voltage rating: 240 Vac, 60 Hz, External mount, Three-pole, Without mounting bracket, Line lead

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Cooper Power series secondary arrester	ASZH240C300
	UPC
	194006066709
<b>Product Length/Depth</b>	<b>Product Height</b>
4.2 in	2.2 in
<b>Product Width</b>	<b>Product Weight</b>
1.3 in	0.905 lb
<b>Compliances</b>	<b>Certifications</b>
IEEE C62-11	Not Applicable

## Accessories

### With line lead

Yes

### With mounting bracket

No

## Electrical Rating

### Frequency rating

60 Hz

### Maximum continuous operating voltage

240 Vac

### Voltage rating

240 Vac

## Type

### Arrester Type

Storm Trapper HE

### Mounting

External

### Number Of Poles

Three-pole

## Resources

### Brochures

[Secondary Arresters and Protective Gaps Catalog](#)

### Catalogs

[Storm Trapper H.E. \(high energy\) low-voltage distribution-class MOV surge arrester catalog](#)

### Installation instructions

[VariSTAR Storm Trapper high energy MOV arrester installation instructions](#)

### Specifications and datasheets

[Overhead line installation and protective equipment specifiers guide](#)

[Eaton Specification Sheet - ASZH240C300](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)