



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street  
72758-6430, AR Rogers  
Phone: 479-636-4190  
Fax: 479-636-5604



## ATC10 10A 32V Blade-Type Fuse Red

*Bussmann Fuses*

Catalog Number	ATC10
Manufacturer	Bussmann Fuses
Description	Motor Fuse-Link, Medium Voltage, 125 A, Ac 3.6 KV, 76 X 359 MM, Back-Up, BS, With Striker
Weight per unit	0.0300 (lbs/each)
Product Category	Tools & Testers

### Features

amperage rating	10 Amp
connection	Blade End
dimensions	1.6300 IN X 1.3800 IN X 0.3800 IN
interrupt rating	1000 Amp
Material	Colored Plastic Housing, Zinc Fuse Element
type of indicators	Non-Indicating
Voltage Rating	32 VDC

### Dimensions and Weight

Size	0.760 In Width X 0.207 In Depth X 0.752 In Height
------	---

### Descriptions

Description	10A 32V BLADE-TYPE FUSE RED
extra long description	BUSS ATC-10 ATC BLADE FUSE - 10 AMP
Features	Automotive blade fuses are the industry standard - used in most domestic and imported cars today. All Bussmann series blade fuses meet or exceed OEM and SAE standards. The easyID indicating blade fuses use LED technology making it easier to spot blown fuses in panels tucked in dark locations.
Long Description	Motor fuse-link, medium voltage, 125 A, AC 3.6 kV, 76 x 359 mm, back-up, BS, with striker
Product Type	Atc Blade Fuse - 10 Amp (5 In Tin)
Special Features	Color Red

### Manufacturer Information

Brand	Eaton
GTIN	00051712703246
Manufacturers Part Number	ATC-10
UPC	051712703246

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Blade fuse



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street  
72758-6430, AR Rogers  
Phone: 479-636-4190  
Fax: 479-636-5604

## Packaging

Carton	5
Weight Per each	0.03

## Uses, Certifications, and Standards

Application	Vehicles: On-Road
standard	UL Listed,RoHS Compliant