

Low Profile Wraparound

FEATURES

- Clear acrylic prismatic diffuser with flat bottom and vertical sides
- Two, three, or four-lamp cross sections
- Hinges from either side
- White steel end plates with flush knockouts for continuous row mounting
- Heavy gauge steel housing die embossed for maximum rigidity
- Heat sink embossments and levelling projections allow direct mounting of HPF fixtures on combustible low density cellulose fiberboard ceilings
- All metal parts are treated with a five stage phosphate bonding process and finished with a baked white enamel
- UL listed 1598, cUL or CSA. Damp Location standard



WRAPS

ORDERING INFORMATION

MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS
AWN 8 ⁵ / ₁₆ " Wide	2 2'	2 Two	14 2', T5: 14 Watt	E Electronic Instant Start (Std.)	U 120V-277V	EL Emergency Battery Pack
AWW 14 ⁵ / ₈ " Wide	4 4'	3 Three	17 2', T8: 17 Watt	3E 3-Lamp Electronic T8, Instant Start	347 347V	GLR Fast Blow Fuse
	8 8'	4 Four	24 2', T5HO: 24 Watt	4E 4-Lamp Electronic T8, Instant Start		NL Incandescent Night Light
		See Product Availability table below.	28 4', T5: 28 Watt	24E (1) 2-Lamp and (1) 4-Lamp Electronic T8, Instant Start		PAF Paint After Fabrication
			32 4', T8: 32, 30, 28 or 25 Watt	EP Electronic T5 or T8, Programmed Start		SB3 Stem Mounting Bracket (Required for 3-Lamp units only)
			54 4', T5HO: 54 Watt	3EP 3-Lamp Electronic T5HO or T8, Programmed Start		NYC NYC Compliant
				4EP 4-Lamp Electronic T5HO (N/A 347V) or T8, Programmed Start		NYCU NYC Compliant, Union Label

ACCESSORIES (ORDER SEPARATELY)

- S18 18" Stem w/Canopy
SS18 18" 45° Swivel Stem w/Canopy

PRODUCT AVAILABILITY

SERIES	NO. OF LAMPS IN CROSS SECTION	NO. OF LAMPS IN FIXTURE	LAMP TYPE	LAMP LENGTH	WIDTH	LENGTH	HEIGHT
AWN2	2	2	14, 17, 24	2'	8 ⁵ / ₁₆ "	2'	2 ⁷ / ₈ "
AWN4	2	2	28, 32, 54	4'	8 ⁵ / ₁₆ "	4'	2 ⁷ / ₈ "
AWN8	2	4	28, 32, 54	4'	8 ⁵ / ₁₆ "	8'	2 ⁷ / ₈ "
AWW4	2	2	28, 32, 54	4'	14 ⁵ / ₈ "	4'	2 ²⁵ / ₃₂ "
	3	3	28, 32, 54	4'	14 ⁵ / ₈ "	4'	2 ²⁵ / ₃₂ "
	4	4	28, 32, 54	4'	14 ⁵ / ₈ "	4'	2 ²⁵ / ₃₂ "
AWW8	2	4	28, 32, 54	4'	14 ⁵ / ₈ "	8'	2 ²⁵ / ₃₂ "
	3	6	28, 32, 54	4'	14 ⁵ / ₈ "	8'	2 ²⁵ / ₃₂ "
	4	8	28, 32, 54	4'	14 ⁵ / ₈ "	8'	2 ²⁵ / ₃₂ "

