



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AYCL153PBR Ariadni 150W Led 3WAY Brown

Lutron

Catalog Number	AYCL153PBR
Manufacturer	Lutron
Description	Dimmer Light, Toggle Switch Type, 120 V, 150 W;6000 W, 60 HZ, Incandescent/Halogen;Dimmable CFL/Led Lamp, Motion Sensor, Wall Mount, 2.86 In Length, 2.58 In Width, 4.60 In Height, Brown, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.2 LB/Ea
Weight per unit	0.2000 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Toggle Switch
connection	Screw Terminal
Connection Type	Screw Terminal
insulation	Plastic
Material	Plastic/Metal
Poles	1
Voltage Rating	120
Wattage	600.0000000000000000

Dimensions and Weight

Size	4.60 x 2.86;117 x 73
------	----------------------

Descriptions

Description	ARIADNI 150W LED 3WAY BROWN
extra long description	LUT AYCL-153P-BR ARIADNI CFL/LED DI
Features	The Ariadni LED+ dimmer provides optimal dimming performance of LED bulbs. This dimmer works with up to 150-Watt of dimmable LED/CFL or 600-Watt of incandescent/halogen, allowing you to control multiple bulb types on the same circuit. It is designed to control a broad range of dimmable LED and CFL bulbs from a variety of brands including Philips, Cree, GE, EcoSmart and Lighting Science. The Ariadni dimmer features a toggle switch to turn your lights off or on-returning the lights to your favorite level. A
Special Features	Controls 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Toggle turn lights on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs as well as halogens and incandescents.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

GTIN 00027557825993
UPC 027557825993

Taxonomies, Classifications, and Categories

Category Description Residential dimmers, motion sensors, controls, & photo cells
Type Preset dimmer, 3-way/single-pole

Packaging

Carton 1
Weight Per each 0.2

Uses, Certifications, and Standards

Application Lighting Control
Enclosure Plastic
environmental conditions Indoor use only
Mounting WALLBOX
Operating Temperature 32 to 104
standard UL1472 CSA C22.2 184.1, NOM