

Eaton B1524S

Catalog Number: B1524S

Eaton B-Line series strut mounting bracket, Conduit and cable, 0.165lbs, Conduit size EMT: 1.5", Rigid: 1.25", Conduit strut clamps, 1.375" Min, 1.66" Max cable diameter, 400 lbs load capacity, Pre-galvanized

General specifications



Product Name	Catalog Number
Eaton B-Line series conduit strut clamp	B1524S
UPC	Product Length/Depth
781011631826	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Certifications
0.165 lb	UL/CUL listed

Model

Product Category

Conduit and cable

Type

Conduit strut clamps

Specifications

Size

Conduit size EMT: 1.5 inch, rigid: 1.25 inch

Load capacity

400 lbs

Cable diameter - min

1.375 in

Cable diameter - max

1.66 in

Resources

Specifications and datasheets

[Eaton Specification Sheet - B1524S](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)