

Eaton B1548S

Catalog Number: B1548S

Eaton B-Line series strut mounting bracket, Conduit and cable, 1" Height, 1" Length, 1" Width, 0.302lbs, Conduit size EMT: 3", Rigid: 3", Conduit strut clamps, 3.250" Min, 3.5" Max cable diameter, 400 lbs load capacity, Pre-galvanized

General specifications

Product Name	Catalog Number
Eaton B-Line series conduit strut clamp	B1548S
UPC	Product Length/Depth
781011632052	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Certifications
0.302 lb	UL/CUL listed

Model

Product Category

Conduit and cable

Type

Conduit strut clamps

Specifications

Size

Conduit size EMT: 3 inch, rigid: 3 inch

Load capacity

400 lbs

Cable diameter - min

3.25 in

Cable diameter - max

3.5 in

Resources

Catalogs

[conduit-and-cable-section-fastener-catalog](#)

[wall-studs-section-fastener-catalog](#)

[Communications and low voltage section fastener catalog](#)

[hangers-section-fastener-catalog](#)

[Fastener-catalog-ruff-IN-pre-fab-section](#)

[beams-section-fastener-catalog](#)

[lathers-channel-section-fastener-catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - B1548S](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia