



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1121 W. 16th Street  
75455-0000, TX Mt. Pleasant  
Phone: 903-577-7311  
Fax: 903-577-7320



## B1B B-Cap Wire Connector, Model B1 Yellow, 500/Bag

*Ideal*

Catalog Number	B1B
Manufacturer	Ideal
Description	Wire Connector, (2) #20 Awg Conductor Size, (3) #12 Awg Conductor Size, Yellow Insulation Color, +221 °F Operating Temperature, 2 to 6 Conductors, 600 V Ac, 0.0034 LB
Weight per unit	0.0030 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

### Material, Color, and Finish

Color	Yellow
-------	--------

### Descriptions

Description	B-CAP WIRE CONNECTOR, MODEL B1 YELLOW, 500/BAG
extra long description	IDEAL B1-B B-CAP B1 YELLOW, 500 BAG
Features	The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you're retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de

### Manufacturer Information

Brand	Buchanan
GTIN	00781789451923
UPC	781789451923

### Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

### Availability

minimum qty	500
Status	Inactive

### Packaging

Carton	500
Package	5000
Weight Per cap	0.003



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1121 W. 16th Street  
75455-0000, TX Mt. Pleasant  
Phone: 903-577-7311  
Fax: 903-577-7320

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS