

Eaton B24-120 GLV

Catalog Number: B24-120 GLV

Eaton B-Line series strut channel, 1.62" H x 120" L x 1.62" W,
Steel, Pre-galv, 14 Gauge



General specifications

Product Name	Catalog Number
Eaton B-Line series strut channel	B24-120 GLV
UPC	Product Length/Depth
781011220303	120 in
Product Height	Product Width
1.62 in	1.62 in
Product Weight	Certifications
14.42 lb	Not Applicable

Model

Channel type

B24

Material/finish

Finish

Pre-galvanized

Material

Steel

Material gauge

14 Gauge

Resources

Brochures

[Strut Channel Identification Overview](#)

Catalogs

[Channel and Combinations Catalog Section](#)

[KwikSplice Cable Tray USA Stocking List Flyer](#)

[Aluminum and Stainless Steel Materials Catalog Section](#)

[Strut Systems Full Catalog](#)

Installation instructions

[KwikSplice Cable Tray System Tab and Lock Trapeze Support](#)

[KwikSplice Splice Plate Instruction Sheet](#)

Specifications and datasheets

[Eaton Specification Sheet - B24-120 GLV](#)

System overview

[Dura-Green finish overview](#)

Technical service bulletins

[KwikSplice Cable Tray Canada Stocking List Flyer](#)