





B-CAP® Wire Connectors

- Four color-coded models cover a full range of wire sizes from 22 AWG to 6 AWG
- Classic Fin™ design provides secure grip for extra leverage on maximum wire combinations
- Live-action spring expands to accept wire shape and size – no pre-twisting required
- Square-wire spring threads directly onto conductors for fast, secure connections
- Deep skirt protects against flash-over and turned-back strands for maximum dielectric protection
- Easily removed for repeat usage on same size or larger wire combinations
- Tough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)
- Green-B® designed for making ground connections and bonding non-metallic sheathed cable
- UL 486C Listed (Green-B® UL 467 Listed) and CSA 22.2 #188 Certified; comply with Federal Specification -S-610E




Model	Color	Wire Combination Range	Wire Combination Range (mm)	Quantity/Package	Cat. No.
 B1	Yellow	600V* 22 to 10 AWG Min. 3 #20 Max. 3 #12	600V* ,34mm² to 6,0mm² Min. 3-,5mm² Max. 3-4,0mm²	Box of 100	B1-1
				Jar of 250	B1-250JR
				Jar of 500	B1-500JR
				Keg of 5,000 (10 bags, 500 ea.)	B1-B
				Barrel of 25,000	B1-SK
 B2	Red	600V* 22 to 8 AWG Min. 2 #18 Max. 5 #12	600V* ,34mm² to 10,0mm² Min. 2-,75mm² Max. 5-4,0mm²	Box of 100	B2-1
				Jar of 350	B2-350JR
				Jar of 500	B2-500JR
				Keg of 5,000 (10 bags, 500 ea.)	B2-B
				Barrel of 25,000	B2-SK
 B4	Blue-Gray	600V* 14 to 6 AWG Min. 2 #12 Max. 2 #6	600V* 2,5mm² to 16,0mm² Min. 2-4,0mm² Max. 2-16,0mm²	Box of 25	B4-1
				Keg of 2,500 (10 bags, 250 ea.)	B4-B
 BGR	Green	14 to 10 AWG Min. 2 #14 Max. 5 #12	2,5mm² to 6,0mm² Min. 2-2,5mm² Max. 5-4,0mm²	Box of 50	BGR-1
				Keg of 2,500 (10 bags, 250 ea.)	BGR-B

*1,000V maximum in fixtures and signs



Wire Connectors

- Wide red/yellow wire range; min. 2 #18 to max. 2 #8
- Rounded dial-top provides fast fingertip starts
- Square-wire spring provides quick, secure connections
- Comfortable swept-wing design with deep skirt to help protect over-stripped wires
- Tough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)
- UL Listed to 486C and CSA Certified to C22.2 #188; comply with Federal Specification W-S-610E

Model	Color	Wire Combination Range	Wire Combination Range (mm)	Quantity/Package	Cat. No.
 BT2™	Red	600V* 18 to 8 AWG Min. 2 #18 Max. 2 #8	600V* ,75mm² to 10mm² Min. 2-,75mm² Max. 2-10,0mm²	Box of 100	BT2-1
				Jar of 500	BT2-500JR
				Barrel of 25,000	BT2-SK

*1,000V maximum in fixtures and signs



Wire Connector
774A

Cu/Cu
Only



LR9706



Wire Connector
774A

Cu/Cu
Only



LR9706