



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB1025 Type Bab Circuit BRKR, 1P, 25AMP, 40C, 120/240V, 10, 000 *Eaton Corp*

| | |
|------------------|---|
| Catalog Number | BAB1025 |
| Manufacturer | Eaton Corp |
| Description | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, High Intensity Discharge, 25 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab |
| Weight per unit | 0.3500 (lbs/each) |
| Product Category | 1 Pole Standard Trip Bolt-On |

Features

| | |
|------------------|-----------------------------------|
| amperage rating | 25 A |
| dimensions | 4.0000 IN X 1.0000 IN X 5.0000 IN |
| interrupt rating | 10 |
| media | Yes |
| Poles | 1 |
| Trip Type | Non-Interchangeable |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|--|
| Description | TYPE BAB CIRCUIT BRKR,1P,25AMP,40C,120/240V,10,000 |
| extra long description | ETN BAB1025 BAB , 1P,25AMP,40C,120/2 |
| Features | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description | Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,25 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB |
| Product Type | Bab , 1P, 25AMP, 40C, 120/240V, 10ka |
| Special Features | High intensity discharge |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton Corp |
| GTIN | 00786679301258 |
| Manufacturers Part Number | BAB1025 |
| UPC | 786679301258 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Thermal magnetic circuit breakers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.35 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Datacenters - IT Space: CI and Hyper Converged Marine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other |
| standard | CSA Certified,UL Listed |