

# Eaton BAB1040

Catalog Number: BAB1040

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 40A, 10 kAIC, 120/240V



## General specifications

|  |                       |
|--|-----------------------|
| <b>Product Name</b>                        | <b>Catalog Number</b> |
| Eaton BAB thermal magnetic circuit breaker | BAB1040               |
|  | <b>UPC</b>            |
|  | 786679301401          |
| <b>Product Length/Depth</b>                | <b>Product Height</b> |
| 3.6 in                                     | 4.8 in                |
| <b>Product Width</b>                       | <b>Product Weight</b> |
| 1.2 in                                     | 0.3 lb                |
| <b>Warranty</b>                            | <b>Certifications</b> |
| 1 year                                     | CSA Certified         |
|  | UL Listed             |
| <b>Catalog Notes</b>                       |                       |
| HACR rated                                 |                       |

## Physical Attributes

### Circuit breaker type

BAB

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Quicklag industrial thermal-magnetic circuit breaker

## Performance Ratings

### Amperage Rating

40 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Quantity

7

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Multimedia

[Circuit Breakers Explained](#)

### Specifications and datasheets

[Eaton Specification Sheet - BAB1040](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)