

Eaton BAB1050

Catalog Number: BAB1050

Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,50 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB



General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton BAB thermal magnetic circuit breaker | BAB1050 |
| | UPC |
| | 786679301500 |
| Product Length/Depth | Product Height |
| 3.8 in | 4.8 in |
| Product Width | Product Weight |
| 1.2 in | 0.35 lb |
| Warranty | Certifications |
| 1 year | UL Listed |
| | CSA Certified |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

BAB

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

50 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Special features

High intensity discharge

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB1050](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)