

Eaton BAB thermal magnetic circuit breaker

BAB1050

UPC:786679301500

Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.8 IN
- **Width:** 1.2 IN

Weight:.35 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Special Features:** High intensity discharge
- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q7
- **Circuit Breaker Type:** BAB

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB1050](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



