

## Eaton BAB thermal magnetic circuit breaker

**BAB1060**

**UPC:**786679301609

**Dimensions:**

- **Height:** 4.6 IN
- **Length:** 3.7 IN
- **Width:** 1.2 IN

**Weight:**.35 LB

**Notes:**HACR rated

**Warranties:**

- 1 year

**Specifications:**

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Amperage Rating:** 60A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q7
- **Circuit Breaker Type:** BAB

**Supporting documents:**

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB1060](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:** No Data

