

Eaton BAB thermal magnetic circuit breaker

BAB2015

UPC:786679302156

Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.8 IN
- **Width:** 2.1 IN

Weight:.65 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag Industrial Circuit Breaker
- **Special Features:** Bolt-on mounting|Switching neutral
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240 V
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q7
- **Circuit Breaker Type:** BAB

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB2015](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



