



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB2020 BRKR A BAB2020~1230C41G12~1230C41G02~BRKR A

Eaton Corp

Catalog Number	BAB2020
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 20 A, Bolt-On, 120/240 V Ac, 3.5 In Overall Height, 2.25 In Overall Length, 6.25 In Overall Width
Weight per unit	1.0 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

amperage rating	20 A
dimensions	2.9060 IN X 2.0000 IN X 2.9060 IN
Poles	2
Trip Type	Non-Interchangeable

Descriptions

Description	BRKR A BAB2020~1230C41G12~1230C41G02~BRKR A
extra long description	ETN BAB2020 20A, 2 pole circuit bre
Special Features	Bolt-on mountingSwitching neutral

Manufacturer Information

GTIN	00786679302200
UPC	786679302200

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	12
Weight Per each	1.03

Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL Listed,CSA Certified