

Eaton BAB thermal magnetic circuit breaker

BAB2030

UPC:786679302309

Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.9 IN
- **Width:** 2.2 IN

Weight:.55 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Special Features:** Switching neutral
- **Amperage Rating:** 30A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 240V
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q7
- **Circuit Breaker Type:** BAB
- **Terminals:** Ring or spade lug terminals

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB2030](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



