

Eaton BAB2030

Catalog Number: BAB2030

Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Switching neutral,30 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB, Ring or spade lug terminals

Photo is representative

General specifications

Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB2030
	UPC
	786679302309
Product Length/Depth	Product Height
3.9 in	4.8 in
Product Width	Product Weight
2.2 in	0.55 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	



Physical Attributes

Circuit breaker type

BAB

Number of poles

Two-pole

Terminals

Ring or spade lug

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

30 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Quantity

7

Special features

Switching neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB2030](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia