

Eaton BAB thermal magnetic circuit breaker

BAB2040

UPC:786679302408

Dimensions:

- **Height:** 2.9 IN
- **Length:** 3.1 IN
- **Width:** 2 IN

Weight:.6 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Special Features:** Bolt-on mounting
- **Amperage Rating:** 40A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240 V
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q7
- **Circuit Breaker Type:** BAB

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB2040](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



