

Eaton BAB2040H

Catalog Number: BAB2040H

Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,40 A,10 kAIC,Two-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase



General specifications

Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB2040H
	UPC
	786679302422
Product Length/Depth	Product Height
3 in	3.5 in
Product Width	Product Weight
2 in	0.65 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

BAB

Number of poles

Two-pole

Number of wires

4

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

40 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Special features

Bolt-on mounting

Used with

Distribution panels 240 V (Three-phase, four-wire maximum)

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB2040H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)